

Ultra Resistant Polyethylene Labels



Media overview

OKI Media Reference	OKIMED18
Supplier	Avery
Supplier Reference	L7914
Media Description	Industrial Labels for extreme conditions (8 per sheet)
Key Characteristics	Stretchable, weather/water/temp (-40 to +150oC) resist
Size	A4
Weight	
Thickness	0,32 mm
Warranty	See Media Statement for the details
IVP Media Proposition	Ultra Resistant Outdoor labels. Weather, temp, water resistant, dirt-repellent
IVP Print Applications	High stress tough conditions e.g. extreme heat, seawater

Media Samples



Ultra Resistant Polyethylene Labels



Device Setup

Device	C824n, C824dn, C834nw, C834dnw, C844dnw
Firmware Level	A01.11_0_4 or later
CMF version	Not required
Media Type	PLAIN
Media Weight	UH3 (Ultra Heavy 3)
Feeding Tray & Orientation	MPT (Multi Purpose Tray) LEF (Long Edge Feeding)
Output Bin	Face-up (Rear Output)
Main Limitations <i>Please refer to the MEDIA Statement for all the details</i>	<p>The coating on the surface of the Media can occasionally cause sheets of Media to stick together and be fed through the paper path simultaneously. If this happens please feed the Media one sheet at a time.</p> <p>Media must be printed from the MP Tray only and exit to the Rear output tray.</p> <p>The pickup roller may leave a visible mark at the top centre of every page being loaded. To avoid this mark, please feed the Media one sheet at a time.</p> <p>Print quality may not be as good around the perforations. If the image being printed goes across the perforation "dirty print" may occur on the printed output. Large curling may occur due to the paper construction of the labels.</p>



MPT LEF Feeding



Face-up Raer Output

Ultra Resistant Polyethylene Labels






Sample Printing Instructions *These instructions are based on C844 model*

- 1 Driver**
- 2 Device setup and preparation**
Open MPT tray and put the media into the tray according to orientation described into «device setup» section
- 3 Printing the file**
Open the PDF file with Acrobat Reader DC and click CTRL+P to open the PRINT interface
- 4 Select the C844 PS printer**
- 5 Configure the paper sizing & handling settings as show in the picture.**
- 6 Click on Properties button to access to the PS driver settings**
- 7 Access to the Paper/Quality tab to configure Paper Source and Media Type according to the setting specified into «device setup» section**

Postscript Version 1.0.1



MPT LEF Feeding




Ultra Resistant Polyethylene Labels




Sample Printing Instructions *These instructions are based on C844 model*


- 8** Please click on Advanced button to access to the interface to setup the Media Weight Ultra Heavy 3 (UH3) and click OK to confirm the setting



- 9** Click Job Option tab to set «Quality» Normal(600x600)



- 10** Click Colour Tab to set Colour Mode on «Automatic» and «Toner Saving» on OFF



- 11** Click OK to register the setting and return to the Adobe Reader DC print Interface

- 12** Click «Print» button to send the data to the printer

